

## Valentines Heart Box

Notes:

This template has been designed using the following criteria:

3.0mm thick materials


Products used in the example #WUS093 - Maple laser wood #CAST300RD-FLR Fluorescent red acrylic.

2" focal lens giving a spot size of 0.127mm. which is a kerf value of 0.0935mm (Spot size/2) = Kerf.

For other focal lenses and material thicknesses adjust accordingly.


Tip: mask both sides of the wood with a low tack application tape Prior to cutting to avoid scorching or staining.

## Wooden Outer Box



## Acrylic Inner Box





**TEMPLATE 1100**